LM Guide Medium-to-low Vacuum Type Model HSR-M1VV



Point of Selection	A1-10			
Point of Design	⊠1-434			
Options	⊠1-457			
Model No.	⊠1-522			
Precautions on Use	⊠1-530			
Accessories for Lubrication	⊠24-1			
Mounting Procedure and Maintenance	B 1-89			
Equivalent moment factor	▲1-43			
Rated Loads in All Directions	A 1-58			
Equivalent factor in each direction	⊠1-60			
Radial Clearance	⊠1-71			
Accuracy Standards	⊠1-76			
Shoulder Height of the Mounting Base and the Corner Radius	⊠1-445			
Permissible Error of the Mounting Surface	⊠1-450			
Flatness of the Mounting Surface				
Dimensions of Each Model with an Option Attached	⊠1-470			



LM Guide

Structure and Features

[Features]

- Operable in various environments at pressure between atmospheric pressure and vacuum (10³ [Pa]).
- Capable of withstanding baking temperature up to 200℃*
- Use of a newly developed labyrinth end seal dedicated for Medium-to-Low Vacuum increases grease retention and allows extended use in vacuum.
- Use of grease designed for Medium-to-Low Vacuum achieves a stable rolling resistance.
- * If the baking temperature exceeds 100°C, multiply the basic load rating with the temperature coefficient.

Structure of the labyrinth end seal dedicated for Mediumto-Low Vacuum

The labyrinth end seal dedicated for Medium-to-Low Vacuum forms a multi-stage space as shown in the figure on the right to minimize the pressure difference between adjacent stages. This reduces the outflow velocity of the oil inside the LM block to a minimum. In addition, the seal will not affect the rolling resistance since it does not contact the LM rail.



[Achievable vacuum level]

The LM Guide for Medium-to-Low Vacuum demonstrates an excellent achievable vacuum level.

[Test conditions] Temperature: 25°C (±5°C)

	HSR15M1RVV	HSR15R (for reference)
Grease	Grease for Medium- to-Low Vacuum	AFB-LF Grease
Seal	Labyrinth end seal dedicated for Medi- um-to-Low Vacuum	None
Endplate	Stainless steel	Resin



Achievable vacuum level

[Rolling resistance]

The grease used in the LM Guide for Mediumto-Low Vacuum has a smaller rolling resistance than conventional fluorine grease and ensures stable rolling motion.

Specimen: HSR15M1RVV Temperature: 25°C (±5°C) Pressure: atmospheric pressure







Types and Features

Model HSR-M1RVV

With this type, the LM block has a smaller width (W) and tapped holes. Used in places where the space for table width is limited.



Precautions on Design

If a large moment is applied to a system consisting of one block on one axis, the labyrinth end seal may contact the rail, and it may affect the motion.

If a moment is applied, we recommend using two axes with two blocks per axis. Contact THK for details.

A1-378 1元HK

冗出版 图1-379

Model HSR-M1VV



	Oute	er dimens	sions								
Model No.	Height	Width	Length								
	М	W	L	В	С	S×ℓ	Lı	т	К	H₃	
HSR15M1R-VV	28	34	75	26	26	M4×5	38.8	6	23.7	4.3	



Note1) The radial clearance, maximum LM rail length and accuracy class are equal to that of model HSR. Note2) With this model, a single-rail unit constitutes one set (i.e., the required number of sets when 2 rails are used in parallel is 2).

▲1-380 元出比



Unit: mm

₩ ▲1-381

LM rail dimensions						Basic load rating		Static permissible moment kN-m*				Mass		
Width		Height	Pitch		Length*	С	C₀	MA				M° (͡͡͡b	LM block	LM rail
W₁ ±0.05	W_2	M1	F	d₁×d₂×h	Max	kN	kN	1 block	Double blocks	1 block	Double blocks	1 block	kg	kg/m
15	9.5	15	60	4.5×7.5×5.3	1240	10.9	15.7	0.0945	0.527	0.0945	0.527	0.0998	0.27	1.5

Note) The maximum length under "Length*" indicates the standard maximum length of an LM rail. (See **⊠1-382**.) Static permissible moment*: 1 block: static permissible moment value with 1 LM block Double blocks: static permissible moment value with 2 blocks closely contacting with each other If a large moment is applied to a system consisting of one block on one axis, the labyrinth end seal may contact the rail, and it may affect the motion. If a moment is applied, we recommend using two axes with two blocks per axis.

Contact THK for details.

LM Guide

Standard Length and Maximum Length of the LM Rail

Table1 shows the standard lengths and the maximum lengths of model HSR-M1VV variations. If the maximum length of the desired LM rail exceeds them, jointed rails will be used. Contact THK for details.

For the G dimension when a special length is required, we recommend selecting the corresponding G value from the table. The longer the G dimension is, the less stable the G area may become after installation, thus causing an adverse impact to accuracy.



Model No.	HSR15M1R-VV
LM rail standard length (L₀)	160 220 280 340 400 460 520 580 640 700 760 820 940 1000 1000 1060 1120 1180 1240
Standard pitch F	60
G	20
Max length	1240

Table1 Standard Length and Maximum Length of the LM Rail for Model HSR-M1VV

A1-382 10HK

Note1) The maximum length varies with accuracy grades. Contact THK for details. Note2) If jointed rails are not allowed and a greater length than the maximum values above is required, contact THK.

Unit: mm

1-383